


The Spare Part List is valid for the following articles:
13587 ENA micro 9 OT EU 230V/50Hz [SCHUKO]

The Variant designations mean:

EXPERT-CM.RU

(1) Case components and water tank

S13587_01




Art.-Nr.	Pos	Designation	Variation	Stock	SC
70119	0101	Tank lid black		X	
70120	0102	Tank base		X	
70122	0103	Watertank BLUE		X	
70129	0104	Emblem Jura back cpl		X	
65799	0105	Screw KST/PT 3x12 vz-sw RoHS		X	
70130	0106	Bolt back black		X	
70123	0107	Bean container cover		X	
70131	0108	Ventilation cover		X	
70126	0109	Switch		X	
70124	0110	Cover at the front		X	
70125	0111	Support		X	
70128	0114	Left side section platinum		X	
70127	0115	Left side section platinum		X	
70121	0119	Bracket Claris BLUE		X	

EXPERT-CM.RU

(2) Case components

S13587_02




Art.-Nr.	Pos	Designation	Variation	Stock	SC
64049	0201	O-ring 100pcs (sep. 59456)		X	
59456	0201	Inner distributing collar		X	
70135	0202	Sieve		X	
70134	0203	Bottom		X	
70133	0204	Interference eliminator		X	
70137	0205	Pipe		X	
70185	0206	Silicone hose 05.0x2.00x315		X	
70187	0207	Silicone hose 05.0x2.00x610		X	
67924	0208	Condens casing		X	
70132	0209	Flowmeter adapter		X	
70186	0210	Silicone hose 05.0x2.00x150		X	
62942	0211	Fillister head screw 3.5x12		X	
70136	0212	Reed sensor MS-324/244C		X	
58640	0213	Angled hose		X	
70188	0214	Silicone hose 05.0x2.00x215		X	
59391	0215	Flowmeter fhksc 12r 0-degree		X	
58636	0216	Retaining ring starlock d=3		X	
68331	0217	Elastic pad		X	

EXPERT-CM.RU

(3) Front cover and cappu.

S13587_03




Art.-Nr.	Pos	Designation	Variation	Stock	SC
62942	0301	Fillister head screw 3.5x12		X	
70090	0302	Front cover platinum		X	
70091	0303	Emblem Jura cpl		X	
70092	0304	Outlet gate classic black		X	
62587	0305	Fillister head screw 3x12		X	
70181	0306	Silicone hose 03.0x1.50x285		X	
70094	0307	Discharge pipe		X	
70093	0308	Outlet gate front platinum		X	
70182	0309	Silicone hose 02.0x1.50x205		X	
70095	0310	Support fluid-system		X	
58916	0311	O-ring silicon 6.75x1.78		X	
70096	0312	Foam nozzle		X	
65101	0313	O-ring 5.00x1.50 Silikon/2-K		X	
70097	0314	Housing bottom black		X	
67656	0315	Air suction		X	
70099	0316	Cap autocappuccino		X	
70100	0317	Plug		X	
70101	0319	Silicone hose 03.0x1.50x360		X	
70358	0320	Jet milk V2 cpl.		X	
70098	0321	Beaker discharge		X	

EXPERT-CM.RU

(4) Support plate and spout

S13587_04




Art.-Nr.	Pos	Designation	Variation	Stock	SC
62942	0401	Fillister head screw 3.5x12		X	
70106	0402	Bracket		X	
70182	0403	Silicone hose 02.0x1.50x205		X	
69062	0404	Silicone hose 3.0x1.50x240		X	
70109	0405	Valve body		X	
70107	0406	Safety element		X	
70184	0407	Silicone hose 02.0x1.50x215		X	
65903	0408	Hose clamping 7.0-7.5 RoHS		X	
64328	0409	Hose FEP 4x2.5x190mm		X	
68057	0410	O-ring 100pcs (sep. 63444)		X	
58625	0411	Clamp		X	
70183	0412	Silicone tissue hose D 3.0		X	
70181	0413	Silicone hose 03.0x1.50x285		X	
70108	0414	Cover		X	
70103	0415	Bolt bracket		X	
70102	0416	Bracket		X	
70104	0417	Connection cappu.		X	
70112	0418	Guide for outlet gate		X	
70105	0419	Support		X	
70110	0420	Support front cover left		X	
70111	0421	Support front cover right		X	

EXPERT-CM.RU

(5) Pan

S13587_05




Art.-Nr.	Pos	Designation	Variation	Stock	SC
70118	0501	Used ground container black		X	
70117	0502	Used ground pan shield		X	
70116	0503	Used ground pan		X	
70359	0504	cup grille cpl.		X	
70113	0506	Drain pan black		X	

EXPERT-CM.RU

(6) Printed power circuit board


S13587_06



Art.-Nr.	Pos	Designation	Variation	Stock	SC
70143	0601	Bean container black		X	
70147	0602	Cover		X	
70146	0603	Hinge		X	
70145	0604	Turn knob grinding adjustment		X	
70144	0605	Turn knob grinding adjustment		X	
70141	0606	Housing lid black		X	
62942	0607	Fillister head screw 3.5x12		X	
70142	0608	Bolt		X	
69122	0609	Terminal 3-terminals		X	
62079	0610	Screw kst/PT		X	
62587	0611	Fillister head screw 3x12		X	
58656	0612	Cable retaining clip		X	
66198	0613	Incoming feeder sw RoHS		X	
70148	0614	Powder funnel lid		X	
70149	0615	Powder funnel black		X	
66286	0616	Transformer 230V		X	
70139	0618	Displaymodul Micro		X	
70140	0619	Power pcb Micro 230V		X	
70152	0620	Knob black		X	
70151	0621	Seal		X	
66623	0622	Microswitch 125-250VAC		X	
70150	0623	Switch support		X	
70153	0624	Switch cover		X	
69123	0625	Microswitch		X	

(7) Fluid system


S13587_07



Art.-Nr.	Pos	Designation	Variation	Stock	SC
70158	0701	Membrane elastic pad V2		X	
66122	0702	Clamping spring D=1.3mm V2		X	
64844	0703	Holder		X	
70189	0704	Silicone tissue hose D 4.2		X	
64048	0705	O-ring 100pcs (sep. 58775)		X	
70157	0706	Pump carrier Sysko		X	
64982	0707	Clamp D=5mm		X	
63190	0708	Thermostat 115C/10A 1NT01L		X	
69981	0709	Clamp to thermostat		X	
69742	0710	Pump SAP.HP4 230V/50Hz		X	
69982	0711	Pump support		X	
68380	0712	Absorber set		X	
70156	0713	Motor UCL13N04B2KZ26		X	
62942	0714	Fillister head screw 3.5x12		X	
58640	0715	Angled hose		X	
67942	0716	Connection I-forme 7.5mm		X	
70188	0717	Silicone hose 05.0x2.00x215		X	
67762	0718	Connection		X	
66289	0719	Dispenser valve thermoblock		X	
58625	0720	Clamp		X	
68057	0721	O-ring 100pcs (sep. 63444)		X	
70190	0722	Hose FEP D4.0/2.50x 155mm		X	
69960	0723	Fluid connection F-forme 90°V4		X	
70155	0724	Cover black righth		X	
70154	0725	Cover black left		X	

(8) Heater


S13587_08



Art.-Nr.	Pos	Designation	Variation	Stock	SC
70161	0801	Lid TB2010		X	
70160	0802	Thermoblock 2010/L 230V/1400W		X	
65798	0803	Oval-headed screw M5x8 RoHS		X	
70197	0804	Sensor thermoblock complete		X	
65689	0805	Insulation		X	
70200	0806	Fused-cord EU 192C (1xE5)		X	
70199	0807	Fused-cord EU 192C (1xE5)		X	
68057	0808	O-ring 100pcs (sep. 63444)		X	
64982	0809	Clamp D=5mm		X	
70192	0810	Connection s L-Form 90°		X	
69992	0811	Clamp STB TB2010		X	
70198	0812	Connecting yellow-green		X	
65701	0813	Connection F 90° V2		X	
62670	0814	Screw M4x8		X	
58625	0815	Clamp		X	
66039	0816	Hose FEP 4x2.5x120mm		X	
70193	0817	Connection s V-Form 55°		X	
64226	0818	Nipple 1-time black		X	
64151	0819	Hose FEP 4x2.5x200mm		X	
70190	0820	Hose FEP D4.0/2.50x 155mm		X	
70189	0821	Silicone tissue hose D 4.2		X	
66122	0822	Clamping spring D=1.3mm V2		X	
64844	0823	Holder		X	
64328	0824	Hose FEP 4x2.5x190mm		X	
64048	0825	O-ring 100pcs (sep. 58775)		X	
69062	0826	Silicone hose 3.0x1.50x240		X	
70162	0827	Ceramic valve 12-24V cpl		X	
70187	0828	Silicone hose 05.0x2.00x610		X	
62942	0829	Fillister head screw 3.5x12		X	
70159	0830	Support TB2010		X	

(9) Grinder

S13587_09




Art.-Nr.	Pos	Designation	Variation	Stock	SC
59507	0901	Collar		X	
70254	0902	Grinder unit 230V		X	
70172	0903	Flange		X	
70170	0904	Funnel		X	
65714	0905	Temp.-feeler Johnson motor		X	
65715	0906	Temp.-feeler support		X	
62942	0907	Fillister head screw 3.5x12		X	
62079	0908	Screw kst/PT		X	
59468	0909	Tubular rivet 4x0.4x10 ms blan		X	
59469	0910	Rubber buffer		X	
70169	0911	Grinder support		X	
70167	0912	Bar		X	
70165	0913	Switch lever		X	
66623	0914	Microswitch 125-250VAC		X	
70168	0915	Clamp		X	
70166	0916	Bar		X	
70163	0917	Guide channel		X	
70164	0918	Reed sensor MS-324/244B		X	
64847	0919	Screw KST/PT 3.5x12 inox		X	
59120	0920	Support		X	

EXPERT-CM.RU

(10) Brew unit

S13587_10



Art.-Nr.	Pos	Designation	Variation	Stock	SC
70173	1001	Brew unit assembled		X	
70175	1002	Drainage valve ready assembled			
64847	1003	Screw KST/PT 3.5x12 inox		X	
64919	1004	O-ring 5.0x3.0 EPDM		X	
70176	1005	Used ground blade		X	
70178	1008	Console motor V2		X	
65870	1009	Encoder V2 RoHS		X	
65537	1010	Clamp to encoder		X	
65743	1011	Screw M5x12 vz-blau Li-K		X	
70179	1012	Geared motor		X	
94394	1013	Fillister head screw M4x8		X	
64928	1014	Washer M4 4.3x12.0x1.0		X	
64817	1015	Elastic pad		X	
70196	1016	O-ring 029.75x3.53			
66756	1017	Sieve V3		X	
70180	1018	Powder funnel		X	
70174	1019	Clamping black		X	
70194	1020	Screw M4x35 vz-blau Li-K.		X	
70184	1021	Silicone hose 02.0x1.50x215		X	
70379	1022	Jumper cable 4col. Micro		X	
70195	1023	Screw M4x10 vz-blau Li-K.		X	

EXPERT-CM.RU

(11) Supplement

S13587_11

1101



Verpackung/
Packing

1110




Betriebsmittel/
Operational funds

1120



Hinweise/
References

1140




Bedienungsanleitung/
Operating instructions

Art.-Nr.	Pos	Designation	Variation	Stock	SC
70234	1101	Styropor 2-stage		X	
70233	1101	Picture carton ENA Micro		X	
69633	1110	Quantimeter black		X	
59633	1110	Cleaning tablets		X	
69806	1120	Instruction sheet bean cont.			
69804	1120	Instruction sheet dual spout		X	
66269	1120	Hotline information sticker		X	
63560	1120	Guarantee Dom. 2-J EU		X	
69783	1140	Instructions ENA micro 9		X	

EXPERT-CM.RU

(1) Scheme power/logic



(2) Fluid System

